

MJPEG Encoder (v01.00.17.01) on HDVICP2 and Media Controller Based Platform

FEATURES

- Supports baseline sequential mode for interleaved data formats (single scan)
- Supports YUV 444 Planar, YUV 422 IBE (YUYV), YUV 422 ILE(UYVY), YUV 420 Semi-Planar and Grayscale chroma sub-sampling formats as input
- Supports all resolutions ranging from 32x32 to 16384x8192 for YUV 420SP, YUV 422ILE and YUV 422IBE and resolutions up to 8192x8192 for YUV444 and YUV400
- Supports sub-frame data synchronization for input and output buffers
- Supports selection of quality level by user
- Supports user-defined quantization tables
- Supports 8-bit and 16-bit quantization tables
- Supports insertion of restart marker
- Supports insertion of JPEG File Interchange Format (JFIF) marker segment
- Supports insertion of comment marker segment
- Supports insertion of Exif marker segment
- Supports insertion of thumbnail in JFIF or Exif marker segment
- Graceful exit under error conditions is supported
- Does not support Arithmetic encoding
- Does not support non-interleaved YCbCr output (multiple scans)
- Does not support encoding inputs with 12-bits per sample
- Does not support encoding of thumbnails. This encoder supports only insertion of encoded thumbnail data provided by the application.
- Supports Privacy Masking till 36 regions in a frame
- Supports Rate Control – VBR and CBR for all input YUV Chroma formats.
- The other explicit features that TI's MJPEG Encoder supports are
 - eXpressDSP Digital Media (XDM IVIDENC2) interface compliant
 - Supports multi-channel functionality
 - Supports booting of HDVICP2
 - Implements different power optimization schemes
 - Independent of any operating system
 - Ability to get plugged in any multimedia frameworks (eg. Codec Engine, OpenMax, GStreamer, etc)

DESCRIPTION

JPEG is an international standard for color image compression. This standard is defined in the ISO10918-1 JPEG Draft International Standard | CCITT Recommendation T.81. JPEG supports baseline sequential mode with both interleaved and non-interleaved input format and progressive mode. MJPEG (Motion JPEG) is JPEG used in video mode (for continuous image encoding/decoding in JPEG format).

PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Performance and Memory Summary

This section describes the performance and memory usage of MJPEG Encoder.

Table 1 Configuration Table

CONFIGURATION	ID
Baseline Sequential Encoder (4:2:0 Semi Planar input and 4:2:0 interleaved output) with quality factor = 50	MJPEG_ENC_001
Baseline Sequential Encoder (4:4:4 Planar input and 4:4:4 interleaved output) with quality factor = 50	MJPEG_ENC_002
Baseline Sequential Encoder (4:2:2 YUYV interleaved input and 4:2:2 interleaved output) with quality factor = 50	MJPEG_ENC_003
Baseline Sequential Encoder (4:2:2 UYVY interleaved input and 4:2:2 interleaved output) with quality factor = 50	MJPEG_ENC_004

Table 2 Cycles Information - Profiled on DM816x REV-A2 EVM with Code Generation Tools Version 5.0.3

CONFIGURATION ID	HDVICP2 PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾		
	TEST DESCRIPTION ⁽²⁾	AVERAGE ⁽³⁾	PEAK ⁽⁴⁾
MJPEG_ENC_001	Motion1_640x360_420SP,Baseline Sequential	13.96	15.54
	Motion1_640x480_420SP,Baseline Sequential	16.99	18.24
	Office_720x480_420SP.xls, Baseline Sequential	18.64	19.74
	Lambhorgini_p1280x720_fps_420SP, Baseline Sequential	43.59	44.87
	Tractor_1920x1080_420SP, Baseline Sequential	98.74	100.61
MJPEG_ENC_002	Motion1_640x360_444P, Baseline Sequential	29.38	31.09
	Motion1_640x480_444P, Baseline Sequential	37.75	38.96
	Office_720x480_444P, Baseline Sequential	41.48	42.97
	Lambhorgini_1280x720_444P, Baseline Sequential	103.47	104.81
	Tractor_1920x1080_444P, Baseline Sequential	228.72	231.59
MJPEG_ENC_003	Motion1_640x360_422IBE_YUYV, Baseline Sequential	121.61	123.36
	Office_720x480_422ILE_YUYV, Baseline Sequential	178.35	180.84
MJPEG_ENC_004	Motion1_640x360_422ILE_UYVY, Baseline Sequential	122.15	123.86
	Motion1_640x480_422ILE_UYVY, Baseline Sequential	160.86	162.60
	Office_720x480_422ILE_UYVY, Baseline Sequential	180.35	182.14
	Lambhorgini_1280x720_422ILE_UYVY, Baseline Sequential	470.77	472.55
	Tractor_1920x1080_422ILE_UYVY, Baseline Sequential	1051.72	1053.43

(1) Measured on DM816x REV-A2 EVM having Cortex-A8 @ 1GHz, HDVICP2 @ 533MHz, Media Controller @ 250 MHz, L3 interconnect @ 500 MHz and DDR2 @ 400 MHz and there could be a variation of around 1-2% in the numbers.

- Media Controller code is placed in cacheable memory region in DDR.
- No latency from system at process call and processing unit as frame (no sub-frame level communication) is assumed.
- All Luma 2D Video buffers of codec being in TILED_8 Bit Memory and all Chroma 2D Video buffers of codec being in TILED_16 Bit Memory.

(2) Streams have been compressed with Quantization Tables and Huffman Tables suggested in the JPEG Standard document.

(3) Measured with rate control disabled. With rate control enabled, additional 2-3 MHz cycles consumption can be expected.

(4) Average is computed based on worst case cycles having 2 extra input frame buffer. Average is calculated @ 30fps.

(5) Peak is based on worst case cycles having no extra input frame buffer. It is computed based on peak among 30 frames @30fps.

(6) Performance is poor for 422UYVY and 422YUYV chroma formats due to HW limitations.

Table 3 Memory Statistics of Media Controller - Generated with Code Generation Tools Version 5.0.3

CONFIGURATION ID	RESOLUTION	PROGRAM MEMORY	MEMORY STATISTICS ⁽¹⁾						TOTAL
			INTERNAL	DATA MEMORY				STACK	
				EXTERNAL ⁽²⁾			CONST		
				PERSISTENT ⁽³⁾		RAW			
TILED8 (numBufs x Width x Height)	TILED16 (numBufs x Width x Height)	TILED PAGE / RAW							
MJPEG_ENC_001 MJPEG_ENC_002 MJPEG_ENC_003 MJPEG_ENC_004	All	11	0	0	0	1.8	229	2	242.8

- (1) All memory requirements are expressed in kilobytes (1 K-byte = 1024 bytes) and there might be rounding to next integer K-byte. Stack can be kept in internal/external memory, negligible performance impact can be observed in Media Controller cycles if it is placed in external memory.
- (2) Codec's request of memory container can be over-riden by application, adhering to the below rules
- TILED PAGE can be overridden by RAW
 - TILED8, TILED16 can be overridden by TILED PAGE, RAW
 - TILED16 can be overridden by TILED8, RAW, TILED PAGE
- However, in case of overriding of 2B and 2C, there can be some performance impact.
- (3) Persistent memory is instance specific and does not include I/O buffers.

Table 4 Split-up of Media Controller Internal Data Memory Statistics

CONFIGURATION ID	DATA MEMORY - INTERNAL ⁽¹⁾		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
MJPEG_ENC_001 / MJPEG_ENC_002 MJPEG_ENC_003 / MJPEG_ENC_004	0	0	0

- (1) Internal memory refers to on chip memory. If the system doesn't have enough internal memory, then external memory can also be used. Memory requirements are expressed in kilobytes.

Notes

- I/O buffers:
 - Input buffer size = 6120 KB (for 1920x1088, YUV444 image)
 - Output buffer size = 4080 KB (considering worst case for 1920x1088, YUV444 image)
- None of the buffers at input and output level is accessed by Media Controller processor hence the data should be valid in DDR (not in cache)
- Total data memory for N non pre-emptive instances = Constants + Runtime Tables + Scratch + N * (Instance + I/O buffers + Stack)
- Total data memory for N pre-emptive instances = Constants + Runtime Tables + N * (Instance + I/O buffers + Stack + Scratch)
- MAIL BOX FIFO #0 and #1 are used and user numbering for Media Controller as 2 and for HDVICP2 as 3 is assumed

- It is assumed that RTS library from ARM is available in system because few symbols like memcpy are used in codec
- All constants and Input/Output Buffers to encoder are assumed to be in VDMA addressable space in DDR

References

- ITU-CCITT recommendation T.81 (reproduction of ISO/IEC 10918-1)
- eXpressDSP Algorithm Interoperability Standard (TMS320 Algorithm Interface Standard)
- MJPEG Encoder on HDVICP2 and Media Controller Based Platform User's Guide

Glossary

Term	Description
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

Acronym	Description
CCITT	Committee Consultative International Telephone and Telegraph
DCT	Discrete Cosine Transform
DRI	Define Restart Interval Marker
DSP	Digital Signal Processing
IEC	International Electrotechnical Commission
ISO	International Organization for Standardization
ITU	International Telecommunication Union
JFIF	JPEG File Interchange Format
JPEG	Joint Photographic Experts Group
MJPEG	Motion JPEG
RST	Restart Marker
XDM	eXpressDSP Digital Media

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2014, Texas Instruments Incorporated